

SSC-760236966E2 | 12 in Pole Top for Ericsson



Top of Pole 12in Dia Concealment Enclosure for up to three Ericsson 220x /440x radios

- Enclosure for holding up to 3 metro cell radios directly below a multiband canister antenna
- Orderable to mount multi-band and multi-port antennas from multiple antenna vendors
- Variable pole diameter mounting kits available to mount to existing structures
- Matching light pole or monopole options available

Pole Top Concealment that can accommodate most antenna manufacturers antennas. Please reach out to your ANDREW Representative for exact model number.

-Supports "V4S4SSP-360S-F2" and "NNV4SSP-360S-F2" antenna with separately ordered "860664552" bracket

Mounts directly to ANDREW poles with no additional mounting materials. Mounts to other wood and metal poles with separately purchased mounts.

Product Classification

| | |
|----------------------|-------------------------------------|
| Product Type | Pole top |
| Product Brand | Metro Cell |
| Ordering Note | ANDREW® standard product with terms |
| Warranty | One year |

General Specifications

| | |
|---|--|
| Antenna Compatibility, ANDREW | ANDREW Canister Antennas |
| Antenna Compatibility, Other Vendors | ACE AMPHENOL DK GALTRONICS GAMMA NU JMA KATHREIN KMW ROSENBERGER |
| Antennas Included | None |
| Color | Light Gray (RAL 7035) |
| Color Options | Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver Signal Black (RAL 9004) Umbra Grey (RAL 7022) White (RAL 9010) |
| Cooling | Passive Cooling |
| Mounting Options | Non-tapered poles Tapered poles Wood poles |
| Radio Compatibility, Ericsson | 220x 440x |
| Radios Included | None |

Dimensions

| | |
|---------------|----------------|
| Height | 762 mm 30 in |
|---------------|----------------|

SSC-760236966E2 | 12 in Pole Top for Ericsson

| | |
|--------------------------------------|--|
| Width | 304.8 mm 12 in |
| Depth | 304.8 mm 12 in |
| Mounting Bolt Circle Diameter | 142.748 mm 5.62 in 241.3 mm 9.5 in |

Material Specifications

| | |
|----------------------------------|------------------|
| Finish Aluminum | Chromate |
| Finish Concealment Covers | Powder coated |
| Material Type | Aluminum Steel |

Environmental Specifications

| | |
|---------------------------|--------|
| Thermal Compliance | GR-487 |
|---------------------------|--------|

Packaging and Weights

| | |
|--------------------------|---|
| Volume | 0.056 m ³ 1.97 ft ³ |
| Weight (unloaded) | 18.144 kg 40 lb |