


SSC-760237600



Middle of Pole Micro Concealment Enclosure for up Low, Mid, and High Power Samsung, Ericsson, and Nokia Radios

- Intended to be used with high powered remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures
- Highly-flexible configuration can house diplexers, AC load center, and/or fiber demarcation

SSC-760237600E1x Ericsson
SSC-760237600E2x Ericsson 4490/4890
SSC-760237600S1x Samsung
SSC-760237600N3x Nokia

Includes Standard Mounting kit for through bolt, clamp, and banding

Available After Market KIts, ordered separately:

- 860649584S-xx 5" Standoff for wood poles
- 860649584ST-xx Standoff for Round Tapered Poles
- 860661938-S1 Nokia to Samsung Retrofit Kit
- 860665118-AMK-002 Nokia to Ericsson 4490/4890 Retrofit Kit

NOTE: 'x' or 'xx' in p/n = color

Product Classification

Product Type	Mid pole
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver Umbra Grey (RAL 7022) White (RAL 9010)
Cooling	Passive Cooling
Mounting Options	Non-tapered poles Tapered poles Wood poles
Power Supply Compatibility	6308 CCI PSU-1200W-48-N DELTA 1.0 DELTA 2.0 PSU-AC-08
Radio Compatibility, Ericsson	220x 440x 4415 4426 4435 4449 4455 4490 4890 8843 Diplexer Power Distribution

SSC-760237600

Radio Compatibility, Nokia AHBCA | AHFIA | AHFIB | AHFIC | AHLBA | CCI | Diplexer | Power Distribution

Radio Compatibility Samsung Diplexer | Power Distribution | RF4402D-D1A | RFV01U-D1A | RT2201-46A | RT4401-48A

Radios Included None

Dimensions

Height 1,117.6 mm | 44 in

Width 533.4 mm | 21 in

Depth 508 mm | 20 in

Electrical Specifications

Power/Fiber Input Trade size knockouts at rear side

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Aluminum | Steel

Environmental Specifications

Thermal Compliance GR-487

Packaging and Weights

Volume 0.303 m³ | 10.7 ft³

Weight (loaded) 136.078 kg | 300 lb

Weight (unloaded) 49.895 kg | 110 lb