SSC-760241465N4 | 12 in Pole Top for Nokia or Samsung



Top of Pole 12in Dia Concealment Enclosure for up to two Airscale Micro radios and/or LAA/CBRS radios or one Samsung LAA or CBRS

- Enclosure for holding 2 Nokia Airscale Micro LAA/CBRS radios
- Orderable to mount multi-band and multi-port antennas from multiple antenna vendors
- Variable pole diameter mounting kits available to mount to existing structures
- Matching light pole or monopole options available
- -Pole Top Concealment that can accommodate most antenna manufacturers antennas. Please reach out to your ANDREW Representative for exact model number.
- -Mounts directly to ANDREW poles with no additional mounting materials. Mounts to other wood and metal poles with separately purchased mounts.
- -Supports (1) "RT4401-48A" or (1) "RT2201-46A" Samsung radio with inlouded adapter bracket. Power Supply to be located in mid pole enclosure.
- -Supports AWHQN with separately available kit "860664329-AMK-001"
- -Supports DK antenna with separately ordered "MTM106001" bracket.
- -Supports "V4S4SSP-360S-F2" and "NNV4SSP-360S-F2" antenna with separately ordered "860664552" bracket

Product Classification

Product TypePole topProduct BrandMetro Cell

Ordering Note ANDREW® standard product with terms

Warranty One year

General Specifications

Antenna Compatibility, ANDREW ANDREW Canister Antennas

Antenna Compatibility, Other Vendors

ACE | AMPHENOL | DK | GALTRONICS | GAMMA

NU | JMA | KATHREIN | KMW | ROSENBERGER

Antennas Included None

Color Light Gray (RAL 7035)

Color Options Beige-Grey (RAL 7006) | Black (RAL 9005) | Black Green (RAL 6012) | Brown

(RAL 8014) | Faux Concrete | Green (RAL 6005) | Metallic Silver | Umbra

Grey (RAL 7022) | White (RAL 9010)

Cooling Passive Cooling

Mounting Options Concrete poles | Metal poles | Non-tapered poles | Tapered poles | Wood

poles

Radio Compatibility, Nokia (2) Airscale micro radios (Including LAA & CBRS models) | AHIA | AHIB | AZRB



SSC-760241465N4 | 12 in Pole Top for Nokia or Samsung

Radio Compatibility Samsung RT2201-46A | RT4401-48A

Radios Included None

Dimensions

 Height
 762 mm | 30 in

 Width
 304.8 mm | 12 in

 Depth
 304.8 mm | 12 in

Mounting Bolt Circle Diameter 142.748 mm | 5.62 in | 241.3 mm | 9.5 in

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Aluminum | Steel

Environmental Specifications

Thermal Compliance GR-487

Packaging and Weights

 Volume
 0.056 m³ | 1.97 ft³

 Weight (unloaded)
 18.144 kg | 40 lb

