## C141-KFKF-M35



CF141 Jumper with interface types 4.1/9.5 PM Female and 4.1/9.5 PM Female, 0.35 m

## **Product Classification**

**Product Type** Braided cable assembly

**Product Series** CF141-50

General Specifications

Body Style, Connector AStraightBody Style, Connector BStraightCable FamilyCF141-50

Interface, Connector A 4.3-10 Female
Interface, Connector B 4.3-10 Female

Specification Sheet Revision Level A

Dimensions

**Length** 0.35 m | 1.148 ft

Nominal Size 0.141 in

**Electrical Specifications** 

**3rd Order IMD** -112 dBm

VSWR/Return Loss

Frequency Band VSWR Return Loss (dB)

**700–3000 MHz** 1.119 25.01

Jumper Assembly Sample Label





## Regulatory Compliance/Certifications

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

