
FE-12106-R11



HELIAX® Fiber and Power Junction Box for 1 Hybrid Trunk, 1 Fiber Trunk, 1 Power Trunk, 8 Hybrid Jumper, Grey Terminal Blocks, 2 Grounding Blocks

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Europe | Latin America | North

America

Product Type Outdoor junction box

Product Brand HELIAX®

General Specifications

Application Used as a fiber/power junction box

Cable Entry, quantity, maximum, bottom 11

Color Gray

Mounting Pipe, 44–114 mm (1.75–4.5 in) OD | Wall

Dimensions

 Height
 317.5 mm | 12.5 in

 Width
 266.7 mm | 10.5 in

 Depth
 152.4 mm | 6 in

Material Specifications

Material Type High-impact polycarbonate, UV resistant

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +75 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +167 \,^{\circ}\text{F})$

Environmental SpaceIndoorOutdoorQualification StandardsIEC 60529:2001, IP67

Packaging and Weights

Included Mounting kit

Weight (unloaded) 6.38 kg | 14.065 lb

ANDREW® an Amphenol company

FE-12106-R11

Weight, net 5.87 kg | 12.941 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

