

# UA-3C



PIM-Guard®, PIM free, Angle member attachment. Includes torque stop set bolt to ensure proper attachment force. Two 3/4" holes for Snap-in style hangers

- Includes torque stop set bolt to ensure proper attachment force

## Product Classification

<b>Product Type</b>	Adapter
<b>Product Brand</b>	PIM-Guard®
<b>Ordering Note</b>	ANDREW® standard product (Global)

## General Specifications

<b>Adapter Type</b>	Angle adapter
<b>Color</b>	Black
<b>Mounting</b>	3/4 in through hole   Angle member
<b>Patent Number</b>	For patents see: <a href="http://www.cs-pat.com">www.cs-pat.com</a>

## Dimensions

<b>Height</b>	44.958 mm   1.77 in
<b>Outside Width</b>	49.022 mm   1.93 in
<b>Inside Length</b>	25.4 mm   1 in
<b>Outside Length</b>	42.672 mm   1.68 in
<b>Compatible Diameter, maximum</b>	11.113 mm   0.438 in
<b>Compatible Diameter, minimum</b>	3.175 mm   0.125 in
<b>Material Thickness</b>	3.175 mm   0.125 in

## Material Specifications

<b>Material Type</b>	Engineered plastic
----------------------	--------------------

## Mechanical Specifications

<b>Installation Torque, maximum</b>	4 ft lb   5.423 N-m
<b>Installation Torque, minimum</b>	3 ft lb   4.067 N-m
<b>Maximum Loading</b>	Triple stack, 1/2 in cable

# UA-3C

---

## Environmental Specifications

<b>Operating Temperature</b>	-20 °C to +85 °C (-4 °F to +185 °F)
<b>UV Resistance, minimum with no degradation</b>	≥1000 hours

## Packaging and Weights

<b>Height, packed</b>	25 cm   9.843 in
<b>Width, packed</b>	14 cm   5.512 in
<b>Length, packed</b>	12 cm   4.724 in
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	0.5 kg   1.102 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

