

AT-10-43-MF



10 dB Coaxial Attenuator DC-6000 4.3-10 M-F

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Attenuator

General Specifications

Device Type	Attenuator
Application	Indoor
Color	Silver
Inner Contact Plating	Silver
Interface	4.3-10 Male
Interface 2	4.3-10 Female
Outer Contact Plating	Trimetal

Electrical Specifications

Return Loss, minimum	20.8 dB
Attenuation	10 dB
Attenuation Tolerance	±0.5 dB
Average Power, maximum	2 W
Impedance	50 ohm
Operating Frequency Band	0 – 6000 MHz
Peak Power, maximum	0.5 kW
VSWR	1.2

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

Regulatory Compliance/Certifications

AT-10-43-MF

Agency

CHINA-ROHS
ROHS
UK-ROHS

Classification

Above maximum concentration value
Compliant/Exempted
Compliant/Exempted

