

# 760242874 | MFC-LCF-09-5Y-12-PACK



Qwik-Fuse Connector, LC, OM3/OM4/OM5, Aqua, for 250µm/900µm, 12 per pack

**OBSOLETE**

Replaced By:

760258743

Qwik-Fuse Connector, LC, OM3/OM4/OM5, Aqua, for 250µm/900µm, 12 per pack

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber connector
<b>Product Brand</b>	LazrSPEED®   Qwik
<b>Product Series</b>	Qwik-Fuse

## General Specifications

<b>Body Style</b>	BTW
<b>Color, boot</b>	Aqua
<b>Color, housing</b>	Aqua
<b>Ferrule Geometry</b>	Factory polished
<b>Interface</b>	LC/UPC
<b>Interface Feature</b>	Field Installable   Fusion splice

## Dimensions

<b>Tube Length</b>	32 mm   1.26 in
<b>Compatible Cable Diameter</b>	0.25 mm   0.01 in   0.9 mm   0.035 in

## Material Specifications

<b>Ferrule Material</b>	Zirconia
-------------------------	----------

## Mechanical Specifications

**Cable Retention Strength, maximum** 0.74 lb @ 0° | 1.03 lb @ 0°

## Optical Specifications

**Fiber Mode** Multimode  
**Fiber Type** OM3 | OM4 | OM5, LazrSPEED® wideband  
**Optical Components Standard** ANSI/TIA-568. 3-D | IEC 61753-1  
**Insertion Loss, maximum** 0.25 dB  
**Insertion Loss, typical** 0.1 dB  
**Return Loss, minimum** 30 dB

## Environmental Specifications

**Operating Temperature** -40 °C to +75 °C (-40 °F to +167 °F)

## Packaging and Weights

**Packaging quantity** 12

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

