



HomeConnect® Power Inserter for Subscriber Amplifiers

OBSOLETE

Replaced By:

CSHMPIE

HomeConnect® Power Inserter for Subscriber Amplifiers with High Isolation, Copper Nickel Plated Zinc Housing

Product Classification

Product Type	Power inserter
Product Brand	HomeConnect®

General Specifications

Device Type	Power inserter
Application	Directs power to the amplifiers by combining the power and RF paths directly

Electrical Specifications

Insertion Loss at Frequency Band, maximum	0.5 dB @ 5–1002 MHz 2.5 dB @ 1125–1675 MHz
Return Loss at Frequency Band, input, minimum	20 dB @ 5–1002 MHz
Return Loss at Frequency Band, output, minimum	20 dB @ 5–1002 MHz
Operating Frequency Band	5 – 1675 MHz
Voltage Range	8–18 Vdc

Electrical Specifications, Isolation

Isolation, port to port	25 dB
--------------------------------	-------

Packaging and Weights

CSMPI

Height, packed	228.6 mm 9 in
Width, packed	228.6 mm 9 in
Length, packed	533.4 mm 21 in
Carton Quantity	500
Weight, gross	16.329 kg 36 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system