

FGS-HMEC-A



FiberGuide® End Cap Kit, 4x4in, Black

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | End cap |
| Product Brand | FiberGuide® |
| Product Series | FGS |

General Specifications

| | |
|---------------------|------------|
| Color | Black |
| Orientation | Horizontal |
| Section Type | End cap |

Dimensions

| | |
|--------------------------|-------------------------------|
| Height | 107.95 mm 4.25 in |
| Width | 39.599 mm 1.559 in |
| Length | 114.427 mm 4.505 in |
| System Dimensions | 102 mm x 102 mm (4 in x 4 in) |

Ordering Tree

FGS-HMEC-A

FGS - HMEC - ¹⁰A - ¹¹Y

Section Size

| | | |
|----|----|-------------------------------------|
| 10 | A | 4 x 4 in |
| | B | 4 x 6 in |
| | C | 2 x 2 in |
| | CA | 2 x 2 in, for vertical slotted duct |
| | D | 4 x 4 in, for vertical slotted duct |
| | E | 4 x 2 in, for vertical slotted duct |
| | F | 4 x 12 in |
| | G | 2 x 6 in |
| | H | 4 x 24 in |
| | M | 4 x 18 in |
| | 24 | 2 x 4 in, for vertical duct |
| | 44 | 2 x 4 in, snap-on for vertical duct |

Section Color

| | | |
|----|-------|--------|
| 11 | empty | black |
| | Y | yellow |

Material Specifications

Material Type Steel

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Included Hardware

Packaging quantity 1

Weight, net 0.103 kg | 0.227 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

