


# SEC4-A5A1D2BA000

---



NOVUX™ SEC Closure, splice only, no adapters, 1x factory-installed 1:2 bare splitter, mounting included, gray

- Design optimized for FTTH façade applications with gray and black colors
- Agnostic to connectivity technologies: splice, connector, field-installable connector for agility and flexibility
- Innovative removable hinge design allows cover to open from the left, right, or top
- Identification plate for either QR code or customer logo
- QR code and CommScope cTrak® app for one-click access to all product information

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Regional Availability Note</b>	Contact your local CommScope representative for specific availability
<b>Product Type</b>	In-line, rectangular fiber closure
<b>Product Brand</b>	NOVUX™
<b>Product Series</b>	SEC100

## General Specifications

<b>Cable Capacity, Branch</b>	2 Round 1.8–7.0 mm (0.07–0.27 in)
<b>Cable Capacity, Drop</b>	6 Round 1.8–7.0 mm (0.07–0.27 in)
<b>Cable Capacity, Feeder</b>	2 Round 9.0–12.0 mm (0.35–0.47 in)
<b>Cable Ports Quantity, total</b>	10 round ports
<b>Cable Sealing Type</b>	Gasket/grommet configuration
<b>Closure Sealing Type</b>	Hinged with lock
<b>Closure Style</b>	In-line
<b>Color</b>	Gray
<b>Mounting</b>	Facade   Wall
<b>Network Area Type</b>	Drop
<b>Port Type</b>	No adapter   No adapter
<b>Splice Tray Included, quantity</b>	3
<b>Splice Tray Type Included</b>	12-way, heat shrink
<b>Splices per Tray, quantity</b>	12
<b>Splicing Capacity, maximum</b>	32


# SEC4-A5A1D2BA000

<b>Splicing Capacity, Single Fusion, maximum</b>	32
<b>Splicing Type, Supported</b>	Single fusion
<b>Splitter Type</b>	1 x 2
<b>Splitter, quantity</b>	1

## Dimensions

<b>Height</b>	117 mm   4.606 in
<b>Width</b>	210 mm   8.268 in
<b>Depth</b>	75 mm   2.953 in

## Ordering Tree



## Optical Specifications

<b>Fiber Type</b>	G.657.A1   G.657.A2   G.657.B3
-------------------	--------------------------------

## Environmental Specifications

<b>Environmental Space</b>	Facade   Outdoor
<b>Qualification Standards</b>	IP55
<b>UV Resistance</b>	UV stabilized

# SEC4-A5A1D2BA000

---

## Packaging and Weights

<b>Included</b>	1x factory-installed 1:2 bare splitter
<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Box   Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

