



CWST wraparound repair sleeve heat shrink kit, unpresurized, for 12 to 55 mm cable diameter, 750 mm long

- Excellent split resistance of the composite structure offers superior resistance to mechanical abuse during and after the installation
- Integrated moisture barrier completely reconstitutes the cable sheath construction

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	EMEA
Product Type	Heat shrink repair sleeve
Product Series	CWST

General Specifications

Color	Black
Sealant Type	Hotmelt adhesive

Dimensions

Length	750 mm 29.528 in
Expanded Inside Diameter, minimum	55 mm 2.165 in
Recovered Inside Diameter, maximum	12 mm 0.472 in
Single Cable Diameter, maximum	55 mm 2.165 in
Single Cable Diameter, minimum	12 mm 0.472 in
Expanded Wall Thickness, minimum	1.1 mm 0.043 in

Material Specifications

Material Type	Fiber-reinforced multi-layer sealing sleeve
----------------------	---------------------------------------------

Environmental Specifications

Environmental Space

Aerial | Buried | Ducted

Packaging and Weights

Packaging quantity

1

Packaging Type

Bag | Carton

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

