



Weatherproofing Kit for Connectors and Splices, includes butyl rubber and PVC tape

## Product Classification

<b>Product Type</b>	Weatherproofing tape
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	ANDREW® standard product (Global)

## General Specifications

<b>Application</b>	Provides additional moisture seal for cable connections
<b>Applications per Kit</b>	Four 1/2 in–7/8 in   Twelve 1/2 in–1/2 in   Twelve 1/2 in–7/8 in to device   Two 1/2 in–2-1/4 in
<b>Harmonized System (HS) Code</b>	4005.91.0000 (Compounded Rubber, Unvulcanized in Plates, Sheets and Strip)

## Dimensions

<b>Nominal Size</b>	1-1/4 in   1-5/8 in   1/2 in   1/4 in   2-1/4 in   3/8 in   5/8 in   7/8 in
---------------------	---

## Material Specifications

<b>Material Type</b>	Butyl rubber tape   PVC tape
----------------------	------------------------------

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +80 °C (+14 °F to +176 °F)
<b>UV Resistance Test Method</b>	Butyl test method in QUV weatherometer cycle of 8 hours UV at 150 °F then 4 hours of condensation at 104 °F   PVC tape test method UL 510, ASTM D1000
<b>UV Resistance, minimum with no degradation</b>	≥1000 hours
<b>Weather Resistance Test Method</b>	04AS00-03.6.0   MIL-STD-1344A, Method 1002

# 221213

---

## Packaging and Weights

<b>Height, packed</b>	195.58 mm   7.7 in
<b>Width, packed</b>	175.26 mm   6.9 in
<b>Length, packed</b>	96.52 mm   3.8 in
<b>Included</b>	One roll of 2 in PVC tape   Six rolls of 2-1/2 in butyl rubber tape   Two rolls of 3/4 in PVC tape
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	1.52 kg   3.351 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

- 42615-10 - Butyl Rubber Tape, 24 in
- 9905-41 - Black 3/4 in PVC Tape, 66 ft
- 9905-71 - Black 2 in PVC Tape, 20 ft