

# 243095-2



Stainless Steel Hardware Kit for 1-1/4 in or 1-5/8 in Block style hangers (3 stack) or 4 mm, 3/8 in, 5/8 in, 1/2 in or 7/8 in Block style hangers (4 stack), includes 3/8 in bolts and hardware, 247.65 mm (9.75 in) length

## Product Classification

<b>Product Type</b>	Hardware kit
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	ANDREW® standard product (Global)

## General Specifications

**Thread Size** 3/8 in

## Dimensions

<b>Maximum Stack Height</b>	4
<b>Length</b>	247.65 mm   9.75 in
<b>Nominal Size</b>	1-1/4 in   1-5/8 in   1/2 in   7/8 in

## Material Specifications

**Material Type** Stainless steel 304

## Packaging and Weights

<b>Height, packed</b>	254 mm   10 in
<b>Width, packed</b>	88.9 mm   3.5 in
<b>Length, packed</b>	88.9 mm   3.5 in
<b>Included</b>	Fifty flat washers   Ten 3/8 in threaded rods   Thirty hex nuts   Twenty lock washers
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	1.361 kg   3 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power