

# 243095-4



Stainless Steel Hardware Kit for 1-1/4 in or 1-5/8 in Block style hangers (3 stack) or 4 mm, 3/8 in, 5/8 in, 1/2 in or 7/8 in Block style hangers (4 stack), includes M10 bolts and hardware, 250.95 mm (9.88 in) length

## Product Classification

|                      |                              |
|----------------------|------------------------------|
| <b>Product Type</b>  | Hardware kit                 |
| <b>Product Brand</b> | HELIAX®                      |
| <b>Ordering Note</b> | ANDREW® non-standard product |

## General Specifications

**Thread Size** M10

## Dimensions

|                             |                                       |
|-----------------------------|---------------------------------------|
| <b>Maximum Stack Height</b> | 4                                     |
| <b>Length</b>               | 250.952 mm   9.88 in                  |
| <b>Nominal Size</b>         | 1-1/4 in   1-5/8 in   1/2 in   7/8 in |

## Material Specifications

**Material Type** Stainless steel 304

## Packaging and Weights

|                           |  |
|---------------------------|--|
| <b>Height, packed</b>     | 259.08 mm   10.2 in  |
| <b>Width, packed</b>      | 119.38 mm   4.7 in   |
| <b>Length, packed</b>     | 30.48 mm   1.2 in  |
| <b>Included</b>           | Sixty flat washers   Ten M10 threaded rods   Thirty hex nuts   Twenty lock washers |
| <b>Packaging quantity</b> | 10   |
| <b>Weight, gross</b>      | 1.819 kg   4.01 lb   |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

# 243095-4

---

\* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power