

244377



Torque Wrench for coupling torque of 7-16 DIN connectors, 1-1/4 in opening

Product Classification

Product Type	Wrench
Product Brand	HELIAX®
Ordering Note	ANDREW® non-standard product

General Specifications

Application	Torques DIN connectors
Calibration	6 mo
Tool Type	Torque wrench

Dimensions

Wrench Opening	31.75 mm 1.25 in
-----------------------	--------------------

Material Specifications

Material Type	Steel
----------------------	-------

Mechanical Specifications

Torque Tolerance	-0/+2
Torque Value	228 in lb 25.761 N·m

Packaging and Weights

Height, packed	381 mm 15 in
Width, packed	73.66 mm 2.9 in
Length, packed	73.66 mm 2.9 in
Packaging quantity	1
Weight, gross	0.89 kg 1.962 lb

Regulatory Compliance/Certifications

244377

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

