

Cold shrink Kit for 27.99 mm (1.1 in) to 13.46 mm (0.52 in) connections

Product Classification	
Product Type	Cold shrink kit
Product Brand	HELIAX®
Ordering Note	ANDREW® standard product (Global)
General Specifications	
Application	Provides additional moisture seal for cable connections
Color	Black
Dimensions	
Length	202.946 mm 7.99 in
Cable Diameter for Seal, maximum	27.99 mm 1.102 in
Cable Diameter for Seal, minimum	13.46 mm 0.53 in
Inner Diameter	53.09 mm 2.09 in
Material Specifications	
Material Type	EPDM rubber
Environmental Specifications	
UV Resistance Test Method	UV condensation reference ASTM-G-53, light source UVA 340 fluorescent lamp
UV Resistance, minimum with no degradation	≥1000 hours
Weather Resistance Test Method	04AS00-03.6.0 IEC 60529:2001, IP67 MIL-STD-1344A, Method 1002
Packaging and Weights	
Height, packed	254 mm 10 in
Width, packed	63.5 mm 2.5 in
Length, packed	63.5 mm 2.5 in



Page 1 of 2

©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 2, 2025

245174

Included	One EPDM rubber tube One sealing foam strip
Packaging quantity	1
Weight, gross	0.16 kg 0.353 lb
Regulatory Compliance/Certifications	

AgencyClassificationCHINA-ROHSBelow maximum concentration valueISO 9001:2015Designed, manufactured and/or distributed under this quality management systemREACH-SVHCCompliant as per SVHC revision on www.andrew.com/ProductComplianceROHSCompliantUK-ROHSCompliant



Page 2 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 2, 2025