


CS-PWRCN



Cold shrink kit for Ericsson RRU power connector or for 27.99 mm (1.1 in) cables to 10.54 mm (0.41 in) connections

Product Classification

Product Type	Cold shrink kit
Product Brand	HELIAX®
Ordering Note	ANDREW® standard product (Global)

General Specifications

Application	Protects connector from corrosion
Color	Gray

Dimensions

Length	152.4 mm 6 in
Cable Diameter for Seal, maximum	27.99 mm 1.102 in
Cable Diameter for Seal, minimum	10.54 mm 0.415 in

Material Specifications

Material Type	Silicone rubber
----------------------	-----------------

Environmental Specifications

UV Resistance Test Method	UV condensation reference ASTM-G-53, light source UVA 340 fluorescent lamp
UV Resistance, minimum with no degradation	≥2000 hours
Weather Resistance Test Method	04AS00-03.6.0 IEC 60529:2001, IP67 MIL-STD-1344A, Method 1002

Packaging and Weights

Height, packed	50.8 mm 2 in
Width, packed	50.8 mm 2 in
Length, packed	177.8 mm 7 in
Included	One Silicone Rubber Tube

CS-PWRCN

Packaging quantity 1
Weight, gross 0.08 kg | 0.176 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

