# ST-SVP30



#### Solar/Video Embedded Communication Pole, 30 ft

- Hinged design
- No climbing necessary for equipment installation
- Single person service
- Secure locking

#### **Product Classification**

Product Type Monopole

### General Specifications

Application Solar | Supervisory Control and Data Acquisition (SCADA)/Video surveillance

Equipment Load Rating Omni antenna | Solar panel | Telecommunications unit

Foundation Embedded

Monopole Capability Type Light duty

Monopole Design Round conical

Optional Accessories Antenna mounts | Ballast mounting kit | Cabinet mounts | Solar mounts | Video mounts

**Dimensions** 

Height9.144 m | 30 ftMounting Diameter, maximum208.28 mm | 8.2 inMounting Diameter, minimum83.82 mm | 3.3 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222-G

## Packaging and Weights

Included Ground tab | Hand holes | Lightning rod | Monopole

Packaging quantity 1

**Weight, net** 120 kg | 264.554 lb



# ST-SVP30

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

