

860649104-XX | Smart Meter Pole Top



The solution is intended to house and conceal a Cimcon smart meter designed to mount directly below a 12 inch Pole Top Module.

- Variable pole diameter mounting kits available to mount to existing structures

Application

This solution is specifically intended for use with PG&E approved Cimcon smart meters.

- As-built, accepts (1) Cimcon iSLC-3100-7P Smart Meter
- As-built, accepts (1) ANSI C136.41 compliant TE 2213362-4, 7- position dimming receptacle
- Compatible with standard Pole Top Concealment mounts which mount multi-band and multi-port antennas from multiple antenna vendors.
- Variable pole diameter mounting kits available to mount to existing wood and metal structures
- Multiple color options available

Product Classification

Product Type	Pole top
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver Pure White
Cooling	Passive Cooling
Mounting Options	Non-tapered poles Tapered poles Wood poles
Radios Included	None

Dimensions

Height	152.4 mm 6 in
Width	304.8 mm 12 in
Depth	304.8 mm 12 in
Mounting Bolt Circle Diameter	142.748 mm 5.62 in 241.3 mm 9.5 in

Material Specifications

Finish Aluminum	Chromate
------------------------	----------

860649104-XX | Smart Meter Pole Top

Finish Concealment Covers Powder coated
Material Type Aluminum | Steel

Environmental Specifications

Thermal Compliance GR-487

Packaging and Weights

Volume 0.011 m³ | 0.4 ft³