

860662430 | Round Straight 8.625" Ladder Height Ports



8.625" diameter pole that accomodates ladder height enclosure installation

Metal pole that supports a variety of installation methods such as poured concrete, embedded pole, pre-cast, and helical foundations
Break Away Compatible
Enclosure mounting ports at 10' AGL
Configurable color and pole height

Foundation Kit Ordered Separately

Product Classification

Product Type	Standard poles
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Color	Galvanized
Color Options	Antique Bronze (SRSL 45893) Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Fairfax Brown (SW 2856) Faux Concrete Federal Park Brown Green (RAL 6005) Light Gray (RAL 7035) Metallic Silver Umbra Grey (RAL 7022) White (RAL 9010)
Compatible Foundation Type	Embedded Pole Embedded with Foam Helical Anchor Poured Concrete Pre-Cast Concrete Split Helical Anchors
Compatible Smart Devices	Cameras Digital Signage Emergency Call Station Environmental Monitoring Security Lighting WIFI

Dimensions

Pole Height Options	11.278 m 37 ft 9.754 m 32 ft
Width	219.075 mm 8.625 in
Luminaire Mount Height	7.315 m 24 ft
Mounting Bolt Circle Diameter	406.4 mm 16 in

Ordering Tree

860662430 | Round Straight 8.625" Ladder Height Ports



Pole Color	
1	Light Grey (RAL 7035)
2	Green (RAL 6005)
3	Black (RAL 9005)
4	Brown (RAL 8014)
5	Beige Grey (RAL 7006)
6	Fairfax Brown (SW 2856)
8	Federal Park Brown
9	Metallic Silver
20	Umbra Grey (RAL 7022)
C	Faux Concrete
F	Signal Black (RAL 9004)
G	Black Green (RAL 6012)
W	White (RAL 9010)
Z	Antique Bronze (SRSL 45893)
0	Galvanized

Pole Height	
32	32 feet (9.8 meters)
37	37 feet (11.3 meters)

Material Specifications

Finish	Powder coated
Material Type	Galvanized steel