

760251611XYS | 12" Pole Base 4G/5G w/ Fluted Riser Shaft



Round 12 inch diameter, Integrated Pole Base Concealment Pole for 4G /5G deployments, with Straight Fluted riser shaft to house and conceal multiple radios and other wireless infrastructure equipment in the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Includes everything needed for a low-power 4G/5G outdoor small cell site
- Up to 4 low power radios, integrated AC load center/OVP and Disconnect , PoleTop concealment module for LAA/DBRS radio mounting

Available After Market Kits, ordered separately:

-860668762- AMK-001 for mounting Ericsson 4435 Radio

ANDREW Cap H Requires additional Radio Module, ordered separately:

-MTM1029-2000-xx Cap H Radio Module for 12" Integrated Poles

Product Classification

Product Type	Integrated pole
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Antenna Compatibility, ANDREW	ANDREW Canister Antennas
Antenna Compatibility, Other Vendors	ACE AMPHENOL GALTRONICS GAMMA NU JMA KATHREIN KMW ROSENBERGER
Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver Umbra Grey (RAL 7022) White (RAL 9010)
Compatible Foundation Type	Poured Concrete Pre-Cast Concrete
Compatible Smart Devices	WIFI
Cooling	Passive Cooling
Radio Compatibility, ANDREW	CAP H
Radio Compatibility, Ericsson	1281 220x 440x 4435 6701 AIR4435

760251611XYS | 12" Pole Base 4G/5G w/ Fluted Riser Shaft

Radio Compatibility, Nokia	(2) Airscale Micro Radios - LAA & CBRS (Pole Top) (2) Airscale micro radios – (radio concealment module) AEUB AEWB AHIA AHIB
Radio Compatibility Samsung	AT1K01 AT1K02 RT2201-46A RT4401-48A
Radios Included	None

Dimensions

Height Note	5 ft tall Equipment Base 5.5 ft tall Radio Concealment Module
Pole Height Options	10.668 m 35 ft 6.096 m 20 ft 7.62 m 25 ft 7.925 m 26 ft 9.144 m 30 ft
Width	325.12 mm 12.8 in
Depth	325.12 mm 12.8 in
Depth Note	Round
Pole Diameter	325.12 mm 12.8 in

Electrical Specifications

Power/Fiber Input	AC load center with OVP and disconnect
--------------------------	--

Material Specifications

Finish Aluminum	Chromate
Finish Concealment Covers	Powder coated
Material Type	Steel

Environmental Specifications

Thermal Compliance	GR-487
---------------------------	--------