


223306-40



Pressure Window for WR229, 3.3–4.9 GHz, mates to PDR40

Product Classification

Product Type Rectangular waveguide, pressure window

General Specifications

Component Pressure Window

Interface UDR40

Mates to Interface PDR40

Dimensions

Waveguide Size WR229 | WG11 | R40

Electrical Specifications

Operating Frequency Band 3.3 – 4.9 GHz

VSWR 1.04

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

