


223306-84



Pressure Window for WR12, 7.05–10.0 GHz, mates to PDR84

Product Classification

Product Type Rectangular waveguide, pressure window

General Specifications

Component Pressure Window

Interface UDR84

Mates to Interface PDR84

Dimensions

Waveguide Size WR112 | WG15 | R84

Electrical Specifications

Operating Frequency Band 7.05 – 10.0 GHz

VSWR 1.04

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

