


D137CCSG



90° Rigid Twist for WR137, 5.85–8.2 GHz, with interface types CPR137G and CPR137G, 12 in, gray

Product Classification

Product Type Rectangular waveguide, rigid twist

General Specifications

Component 90° Rigid Twist

Interface CPR137G

Interface 2 CPR137G

Dimensions

Length 305 mm | 12.008 in

Waveguide Size WR137 | WG14 | R70

Electrical Specifications

Operating Frequency Band 5.85 – 8.2 GHz

VSWR 1.06

Material Specifications

Finish Gray

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system