

MC-CGB10M-B



3-Sector Cage Mount Monopole Platform Base Kit w/ Equip Rig Point, 12 in to 50 in OD, 10 ft 6 in face, pipe ordered separately

OBSOLETE

This product was discontinued on: December 12, 2022

Replaced By:

MC-PM10M-BC

ATLAS 10 ft Monopole Platform with Top Rail Kit. Antenna Pipe Sold Separately.

Product Classification

Product Type Co-location platform

General Specifications

Mounting Monopole, 304.8–1270 mm (12–50 in) OD

Pipe, quantity 0

Sectors, quantity 3

Dimensions

Height 3048 mm | 120 in

Face Width 3.2 m | 10.5 ft

Width 3,200.4 mm | 126 in

Face Support Pipe Diameter 73.66 mm | 2.9 in

Mounting Diameter, maximum 1270 mm | 50 in

Mounting Diameter, minimum 304.8 mm | 12 in

Pipe Outer Diameter 60.96 mm | 2.4 in

Material Specifications

Material Type Hot dip galvanized steel

MC-CGB10M-B

Mechanical Specifications

| | |
|--------------------------------|---|
| Wind Rating | For Specifications, please contact your local ANDREW representative |
| Wind Rating Test Method | TIA/EIA-222 |

Packaging and Weights

| | |
|---------------------------|--|
| Included | Pipe mounts Platform Rail Ring mount |
| Packaging quantity | 1 |
| Weight, net | 571.526 kg 1260 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|-----------------------------------|
| CHINA-ROHS | Above maximum concentration value |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |



* Footnotes

| | |
|--------------------|--|
| Wind Rating | BWS—Base Wind Speed; FBC—Florida Building Code |
|--------------------|--|