


# RR-B2B-AR

---



Low Profile Access Ready RRU Mount Kit for Back-to-Back Mounting of (2) RRUs to Round Members 2-3/8" to 3-1/2" OD

## Product Classification

<b>Product Type</b>	Remote radio head unit mount
<b>Ordering Note</b>	ANDREW® non-standard product
<b>Warranty</b>	One year

## General Specifications

<b>Mounting</b>	Pipe, 60.3–88.9 mm (2-3/8 in to 3-1/2 in) OD
-----------------	--

## Dimensions

<b>Height</b>	340.36 mm   13.4 in
<b>Length</b>	462.28 mm   18.2 in
<b>Mounting Diameter, maximum</b>	88.9 mm   3.5 in
<b>Mounting Diameter, minimum</b>	60.96 mm   2.4 in

## Material Specifications

<b>Material Type</b>	Hot dip galvanized steel
----------------------	--------------------------

## Packaging and Weights

<b>Included</b>	Clamps   Hardware
<b>Packaging quantity</b>	2
<b>Weight, net</b>	16.329 kg   36 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



\* Footnotes

**Warranty**

For more information, please consult our Product Warranty guidelines