BNC-27

Straight BNC Coax Connectors, 7530

OBSOLETE

This product was discontinued on: October 8, 2020

Product Classification

Regional Availability	North America
Product Type	Broadcast video connector

General Specifications

Body Style	Straight
Compatible Cable type	RG 7530
Inner Contact Attachment Method	Crimp
Interface	BNC Male
Outer Contact Attachment Method	Crimp

Electrical Specifications

Connector Impedance	75 ohm
Insulation Resistance, minimum	200 MOhm
Voltage Rating	1000 V

Mechanical Specifications

Attachment Durability	500 cycles

Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Storage Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Relative Humidity	0%–95%, non-condensing
Flammability Rating	UL 94 V-0

Packaging and Weights

Packaging quantity	1

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 6, 2023

COMMSCOPE®

BNC-27

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 6, 2023