1-2055578-3

MPOptimate® Trunk Cable, 24 fiber, duplex, OM4, 13 m, aqua

OBSOLETE

Replaced By:

AJXMPMPAF	OM4 MPO12 (female) to MPO12 (female), Fiber Trunk Cable Assembly, 24-Fiber, Method A, Low Smoke Zero Halogen

Product Classification

Regional Availability	Asia | Australia/New Zealand | China | EMEA | Europe | India
Portfolio	NETCONNECT®
Product Type	Fiber trunk cable assembly
Product Brand	MPOptimate®

General Specifications

Color, boot A	Black
Color, boot B	Black
Color, connector A	Mustard
Color, connector B	Mustard
Connector A, quantity	2
Connector B, quantity	2
Interface, Connector A	MPO-12/UPC Female
Interface, Connector B	MPO-12/UPC Female
Jacket Color	Aqua
Polarity	Pairs, straight
Total Fibers, quantity	24

Dimensions

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: April 6, 2021

COMMSCOPE®

1-2055578-3

Cord Length	13 m | 42.651 ft
Diameter Over Jacket	8 mm | 0.315 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4
Insertion Loss, maximum, connector A	0.35 dB
Insertion Loss, maximum, connector B	0.35 dB
Return Loss, minimum, connector A	28 dB
Return Loss, minimum, connector B	28 dB

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Packaging quantity	1

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: April 6, 2021