760196105

TeraSPEED® MPO (female) to LC Simplex, InstaPATCH® 360 TM Array Fanout, 12-Fiber, Plenum, 50 ft + 24 in Breakout

Product Classification

Regional Availability	Asia | Australia/New Zealand | EMEA | Latin America | North America
Portfolio	SYSTIMAX®
Product Type	Fiber fanout cable assembly
Product Brand	InstaPATCH® 360 | TeraSPEED®
Ordering Note	Fixed length assembly

General Specifications

Color, connector A	Green
Color, connector B	Green
Construction Type	InstaPATCH® 360 array cord
Fibers per Subunit, quantity	12
Furcation Color	Yellow
Interface, Connector A	MPO-12/APC Female
Interface, Connector B	LC/UPC
Jacket Color	Yellow
Total Fibers, quantity	12

Dimensions

Breakout Length	24 in

Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Type	G.652.D and G.657.A1 , TeraSPEED® | OS2

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Plenum

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: December 16, 2020

COMMSCOPE®

760196105

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

860366137	–	MPO12, LOW LOSS, FEMALE, SM, GREEN, 3mm
P-012-MP-8W-F30YL	–	TeraSPEED® Plenum MPO Light Duty Patchcord Cable, 12 fiber

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: December 16, 2020