



One 4" Port Entrance Panel 7" x 7"

## Product Classification

<b>Product Type</b>	Entrance panel
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	ANDREW® non-standard product

## General Specifications

<b>Color</b>	Gray
<b>Entry Panel Port Size</b>	101.6 mm   4 in
<b>Number of Ports</b>	1
<b>Panel Type</b>	Single

## Dimensions

<b>Height</b>	177.8 mm   7 in
<b>Width</b>	177.8 mm   7 in

## Material Specifications

<b>Material Type</b>	Aluminum
----------------------	----------

## Environmental Specifications

<b>Weather Resistance Test Method</b>	04AS00-03.9.0   IEC 60529:2001, IP66
---------------------------------------	--------------------------------------

## Packaging and Weights

<b>Height, packed</b>	180.34 mm   7.1 in
<b>Width, packed</b>	180.34 mm   7.1 in
<b>Length, packed</b>	180.34 mm   7.1 in
<b>Included</b>	Entry cap   Hardware   Port
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	0.28 kg   0.617 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

## Included Products

CAP-4 – Snap-in Entry Port Cap, 4"

# CAP-4

---



## Snap-in Entry Port Cap, 4"

### Product Classification

<b>Product Type</b>	Port cap
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	ANDREW® non-standard product

### General Specifications

<b>Color</b>	Black
<b>Entry Panel Port Size</b>	101.6 mm   4 in
<b>Panel Type</b>	Multiple

### Material Specifications

<b>Material Type</b>	Engineered plastic
----------------------	--------------------

### Packaging and Weights

<b>Height, packed</b>	127 mm   5 in
<b>Width, packed</b>	127 mm   5 in
<b>Length, packed</b>	248.92 mm   9.8 in
<b>Included</b>	Entry cap
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	0.02 kg   0.044 lb

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant

