SFG23RHDXL-15-B

G23RHDXL PIM OPTIMIZED SPACING High Capacity Sector Frame with extended 10' Spine for RRU Mounting & extended frame for sites requiring increased sector to sector antenna spacing. 2 7/8in OD x 15ft face. Antenna pipes sold separately.

Product Classification

Product Type	High capacity Tower sector frame
Product Brand	PIM-guard
Product Series	G2

General Specifications

Mounting	Angle 60°, 203.2 mm (8 in) | Straight or tapered legs up to 203.2 mm (8 in) OD
Patent Number	For patents see: www.cs-pat.com
Pipe, quantity	0
Sectors, quantity	1
Tower Taper	Non-tapered | Tapered

Dimensions

Height	838.2 mm | 33 in
Face Width	4.572 m | 15 ft
Width	4,572 mm | 180 in
Face Support Pipe Diameter	73.025 mm | 2.875 in
Mounting Diameter, maximum	203.2 mm | 8 in
Mounting Diameter, minimum	38.1 mm | 1.5 in
Pipe Outer Diameter	73.025 mm | 2.875 in
Stand-off Distance	1,549.4 mm | 61 in

Material Specifications

Material Type	Hot dip galvanized steel

Mechanical Specifications

Wind Rating	For Specifications, please contact steelproducts@commscope.com or call 800-255-1479
Wind Rating Test Method	TIA/EIA-222-G

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 19, 2024

Packaging and Weights

Included	Frame | Stiff arms (2) | Tower attachment
Packaging quantity	1

* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 19, 2024