L4-CLAMP-2B

KwikClamp™ Hanger for 1/2 in coaxial cable, double stack; includes hardware

Product Classification

Product Type	Hanger kit
Product Brand	KwikClamp™
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa | Minimum order quantity (MOQ) is 1 box

General Specifications

Cables per Hanger	1
Color	Black
Hanger Type	KwikClamp™ hanger
Mounting	3–25 mm angle iron | 3–25 mm flat plate | Round Member 8-25 mm

Dimensions

Maximum Stack Height	2
Height	143 mm | 5.63 in
Width	32 mm | 1.26 in
Length	42 mm | 1.654 in
Compatible Diameter, maximum	17 mm | 0.669 in
Compatible Diameter, minimum	15 mm | 0.591 in
Nominal Size	1/2 in
Hanger Spacing, maximum	1.83 m | 6.004 ft

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 14, 2024

L4-CLAMP-2B

Material Specifications

Material Type	Engineered plastic | Stainless steel

Mechanical Specifications

Vibration Survival	≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Corrosion Resistance, minimum with no degredation	≥500 hours in salt spray chamber
Environmental Strength Capability	Five times cable weight
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	15.5 cm | 6.102 in
Width, packed	30.5 cm | 12.008 in
Length, packed	35.5 cm | 13.976 in
Included	Hardware
Packaging quantity	66
Weight, gross	8.1 kg | 17.857 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 14, 2024