



## NOVUX™ CSC Compact Splice Closures

Designed for FTTX drop applications, NOVUX™ CSC100 and CSC40 compact closures are easily configurable and are available in high volumes to meet demand. From the beginning, NOVUX™ CSC100 and CSC40 compact closures were designed for ease of installation and access. And because we began with that goal in mind, your technicians will love the way this totally new component simplifies their fieldwork. Featuring built-in mounting clips and straps, they're easily and quickly mounted on nearly any surface. And to ease installation and maintenance, CommScope's mounting bracket can be used in all applications.

NOVUX™ CSC100 and CSC40 compact closures come with a QR code that allows installers to access CommScope's cTrak® app. With one click, cTrak provides a wealth of product information, specifications, installation instructions, videos, schematics, and test results. NOVUX™ CSC100 and CSC40 compact closures offer an optional customer configurable ID plate to ease network record-keeping.

The CSC100 closure is offered in two types:

- **CSC3:** Color is black (RAL 9005)
- **CSC4:** Color is gray (RAL 7035)

The CSC40 closure is offered in two types:

- **CSC1:** Color is black (RAL 9005)
- **CSC2:** Color is gray (RAL 7035)

Key features of the NOVUX™ closures:

- NOVUX™ is the industry's most flexible FTTX platform. It takes modularity to new levels with technologies that span the end-to-fiber network from the trunk to the drop. That makes it the go-to FTTX platform for virtually every application today and in the future.
- NOVUX™ was designed from the ground up to help service providers gain access to the supplies they need –when and where they need them. And with the power of CommScope's global supply chain, service providers can trust that they'll be able to tackle even the largest FTTX deployments.
- With NOVUX™, ordering, configuration, and training are all easier on the service provider's staff. With common components and installation procedures, it helps overcome craft labor shortages and reduce field errors, too.


## Product Classification

<b>Regional Availability</b>	Asia   EMEA   Latin America   North America
<b>Product Type</b>	Single-ended, rectangular fiber closure
<b>Product Brand</b>	NOVUX™
<b>Product Series</b>	CSC 100   CSC 40

## General Specifications

<b>Cable Ports Quantity, total</b>	3 round ports + 6 multi-out ports (12 cables)
<b>Cable Sealing Type</b>	Compressed gel
<b>Closure Sealing Type</b>	Hinged with latch
<b>Closure Style</b>	Single-ended
<b>Mounting</b>	Pole   Wall

## Ordering Tree



## Environmental Specifications

<b>Environmental Space</b>	Outdoor
<b>UV Resistance</b>	UV stabilized

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



