RDT-SM12J00P2139A



RapidFiber® Mini-RDT Distribution Terminal, 12-fiber, SC/APC, plenum cable, 700 ft

- Designed to provide a quick and simple solution for installing fiber in small and medium sized MDU's
- Incorporates a unique fiber cable spooling system that stores up fiber cable within the enclosure
- Removes the need for field termination and extensive site survey inspections

Product Classification

| Regional Availability | North America |
|-----------------------|-----------------------------|
| Product Type | Fiber distribution terminal |
| Product Brand | RapidFiber® |
| Product Series | Mini-RDT |

General Specifications

| Adapters, quantity | 12 |
|----------------------|----------------------------|
| Cable Entry Location | Bottom left Bottom right |
| Cable Type | Plenum - Stranded |
| Color | Gray |
| Interface | SC/APC |
| Interface, stub | MPO |
| Mounting | Wall |
| Port, quantity | 12 |
| | |

Dimensions

| Height | 200 mm 7.874 in |
|----------------------|-------------------|
| Width | 140 mm 5.512 in |
| Depth | 60 mm 2.362 in |
| Cable Length | 213.36 m 700 ft |
| Outer Cable Diameter | 3 mm 0.118 in |


Dimension Drawing

Page 1 of 3


©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 10, 2023



RDT-SM12J00P2139A



Ordering Tree



Page 2 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 10, 2023

152 meters (500') 168 meters (550') 183 meters (600') 198 meters (650')



RDT-SM12J00P2139A

Material Specifications

Material Type

Plastic

Optical Specifications

Fiber Mode

Singlemode

Indoor

Environmental Specifications

Environmental Space

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

1

| Agency | Classification |
|------------|---|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |
| | |



Page 3 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 10, 2023

