

760067157 | PNL-BK-012-MFA-LC02-BG-SHUTTERED



1000-type Adapter Pack, with 6 OptiSPEED® MM duplex LC adapters, beige

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter pack
Product Brand	OptiSPEED®
Product Series	1000-style

General Specifications

Application	Used in conjunction with G2 1U, 2U and 4U adapter panel shelves, surface mount and raised floor enclosures
Adapter Color	Beige
Adapter Cutout, quantity	12
Adapters, quantity	6
Body Style	Duplex
Interface	LC/UPC
Pigtails Included, quantity	0
Shuttered	Yes

Optical Specifications

Fiber Mode	Multimode
-------------------	-----------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



760067157 | PNL-BK-012-MFA-LC02-BG- SHUTTERED

Included Products

760056010 – OptiSPEED® LC Duplex Low Profile Shuttered Adapter, Beige, Single Pack
MFA-LC02-BG/LP-SHUTTERED

760056010 | MFA-LC02-BG/LP-SHUTTERED



OptiSPEED® LC Duplex Low Profile Shuttered Adapter, Beige, Single Pack

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter
Product Brand	OptiSPEED®
Product Series	MFA

General Specifications

Body Style	Duplex
Color	Beige
Interface	LC/UPC
Interface Feature	Reduced footprint
Mounting	No flange
Shuttered	Yes
Total Ports, quantity	2
Transmission Standards	TIA/EIA-568-B.3 TIA/EIA-604 FOCIS-3

Material Specifications

Alignment Sleeve Material	Phosphorous bronze
----------------------------------	--------------------

Optical Specifications

Fiber Mode	Multimode
-------------------	-----------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

760056010 | MFA-LC02-BG/LP-SHUTTERED

ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

