

# 760242260 | Pole Base 4G/5G, Round 18 in dia



Round 18 inch diameter, Integrated Pole Base Concealment Pole for 4G/5G deployments, to house and conceal multiple radios and any other wireless infrastructure equipment in the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Includes everything needed for a low to mid power 4G/5G outdoor small cell site
- Pole top concealment module for LAA/CBRS radio mounting
- Base of 18in diameter accepts low power radios or mid-power dual band radios
- Concealment integrates AC load center/OVP and disconnect

## Product Classification

**Product Type** Metro cell site enclosure

## General Specifications

**Color** Light Grey (RAL 7035)

**Color Notes** 760242260AB1HH - Light Grey | 760242260AB2HH - Green | 760242260AB3HH - Black | 760242260AB4HH - Brown | 760242260AB5HH - Beige-Grey | 760242260AB9HH - Metallic Silver | 760242260ABCHH - Faux Concrete | 760242260ABWHH - Pure White

**Color Options** Beige-Grey (RAL 7006) | Black | Brown (RAL 8014) | Faux Concrete | Green (RAL 6005) | Metallic Silver | Pure White

**Cooling** Fan Cooling

**Radio Compatibility, Ericsson** (3) 2205/2208 (Pole Top) | (6) 2203/2205/2208 radios | 5G Expansion module included | 760242260E

**Radio Compatibility, Nokia** (1) Airscale Dual Band 160W + (2) AirScale micro radios | (1) Airscale Dual Band 320W | (2) Airscale micro radios – LAA & CBRS (Pole Top) | (4) Airscale micro radios (Base) | 5G Expansion module included | 760242260N

**Radios Included** None

## Dimensions

**Height Note** 10 ft tall Equipment Base

**Pole Height Options** 10.668 m | 35 ft | 12.192 m | 40 ft | 6.096 m | 20 ft | 7.62 m | 25 ft | 9.144 m | 30 ft

**Depth** 457.2 mm | 18 in

**Depth Note** Round

**Pole Diameter** 203.2 mm | 8 in

# 760242260 | Pole Base 4G/5G, Round 18 in dia

---

## Electrical Specifications

**Power/Fiber Input** AC load center with OVP and disconnect

## Material Specifications

**Finish Aluminum** Chromate

**Finish Concealment Covers** Powder coated

**Material Type** Steel

## Environmental Specifications

**Thermal Compliance** GR-487

## \* Footnotes

**Pole Height Options** Overall AGL Standard Height