

# 760242715 | 12" Straight Integrated Pole 4G/5G



Straight 12inch diameter, Integrated 4G/5G capable, Concealment Pole, to house and conceal four low-power radios and any other wireless infrastructure equipment inside pole modules.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Includes everything needed for a low-power 4G/5G outdoor small cell site
- Up to 4 low power radios, integrated AC load center/OVP and Disconnect , PoleTop concealment module for LAA/DBRS radio mounting

Available After Market Kits, ordered separately:

-860668762- AMK-001 for mounting Ericsson 4435 Radio

ANDREW Cap H Requires additional Radio Module, ordered separately:

-MTM1029-2000-xx Cap H Radio Module for 12" Integrated Poles

## Product Classification

<b>Product Type</b>	Integrated pole
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	ANDREW® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Antenna Compatibility, ANDREW</b>	ANDREW Canister Antennas
<b>Antenna Compatibility, Other Vendors</b>	ACE   AMPHENOL   GALTRONICS   GAMMA NU   JMA   KATHREIN   KMW   ROSENBERGER
<b>Antennas Included</b>	None
<b>Color</b>	Light Gray (RAL 7035)
<b>Color Options</b>	Beige-Grey (RAL 7006)   Black (RAL 9005)   Black Green (RAL 6012)   Brown (RAL 8014)   Faux Concrete   Green (RAL 6005)   Metallic Silver   White (RAL 9010)
<b>Compatible Foundation Type</b>	Poured Concrete   Pre-Cast Concrete
<b>Compatible Smart Devices</b>	Cameras   Digital Signage   Emergency Call Station   Environmental Monitoring   Security Lighting   WIFI
<b>Cooling</b>	Passive Cooling
<b>Radio Compatibility, ANDREW</b>	CAP H
<b>Radio Compatibility, Ericsson</b>	(3) 2205/2208 (Pole Top)   (4) 2203 (radio concealment)

# 760242715 | 12" Straight Integrated Pole 4G/5G

---

module) | 1281 | 4435 | 6701 | 6705

## Radio Compatibility, Nokia

(2) Airscale Micro Radios - LAA & CBRS (Pole Top) | (2) Airscale micro radios - (radio concealment module) | AHIA | AHIB | AZRB | Airscale micro

## Radio Compatibility Samsung

AT1K01 | AT1K02 | RT2201-46A | RT4401-48A

## Radios Included

None

## Dimensions

### Height Note

5.5 ft tall Radio Concealment Module | 8 ft tall Power Module Base

### Pole Height Options

10.668 m | 35 ft | 12.192 m | 40 ft | 6.096 m | 20 ft | 7.62 m | 25 ft | 9.144 m | 30 ft

### Depth

325.12 mm | 12.8 in

### Depth Note

Round

### Pole Diameter

325.12 mm | 12.8 in

## Electrical Specifications

### Power/Fiber Input

AC load center with OVP and disconnect

## Material Specifications

### Finish Aluminum

Chromate

### Finish Concealment Covers

Powder coated

### Material Type

Steel

## Environmental Specifications

### Thermal Compliance

GR-487