

# 760072843 | VCM-DS-96-10

Vertical Cable Management Kit, 10in X 96in (254mm X 2438mm) Double Sided, With Doors, Silver

## OBSOLETE

This product was discontinued on: January 31, 2020

### Replaced By:

760244801  
VCM-DS-96-10

Vertical Cable Management Kit, 10in X 96in (254mm X 2438mm) Double Sided, With Doors, Silver

## Product Classification

**Regional Availability** Asia | Australia/New Zealand | EMEA | Latin America | North America

**Portfolio** CommScope®

**Product Type** Vertical cable management

## General Specifications

**Configuration Type** Double-sided

**Color** Silver

**Door, quantity** 2

## Dimensions

**Height** 2,438.4 mm | 96 in

**Width** 254 mm | 10 in

**Depth** 558.8 mm | 22 in

## Material Specifications

**Finish** Powder-coated, smooth

**Material Type** Aluminum

## Environmental Specifications

**Safety Standard** UL | cUL

## Packaging and Weights

**Included** Four 1/2-20 hex nuts | Four 1/2-20 x 1 in hex head bolts | Four flat washers | Instruction sheet | Two spools

**Packaging quantity** 1  
**Packaging Type** Assembled

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant



## Included Products

760073007 - Cable Management Spool, 2 Spools  
CABLE-MGT-SP

# 760073007 | CABLE-MGT-SP



Cable Management Spool, 2 Spools

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Cable management hardware

## General Specifications

<b>Color</b>	Black
--------------	-------

## Material Specifications

<b>Material Type</b>	Plastic
----------------------	---------

## Environmental Specifications

<b>Safety Standard</b>	UL   cUL
------------------------	----------

## Packaging and Weights

<b>Packaging quantity</b>	2
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

