



FACEPLATE KIT, NO-LABEL, 1 GANG, 1 PORT, ELECTRIC IVORY

- Engineered for residential and commercial applications from classrooms and hospitals to offices and homes
- Labeling models feature mold-over icon and leveling and convex labels for maximum visibility in low density areas

Product Classification

| | |
|------------------------------|----------------------------------------------------------------------|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Faceplate kit |
| Product Series | FP-NLBL |
| Warranty | For more information, please consult our Product Warranty guidelines |

General Specifications

| | |
|------------------------------|-----------------------------------------------------------------------------------------------------|
| Application | Used with KJ Series outlets with adapter Used with M Series outlets Used with SL Series outlets |
| Color | Electrical ivory |
| Gangs, quantity | 1 |
| Mounting | Flush |
| Outlet Orientation | Flat |
| Port Marking Type | Icon Non-Label |
| Total Ports, quantity | 1 |

Dimensions

| | |
|---------------|----------------------|
| Height | 115.824 mm 4.56 in |
| Width | 71.374 mm 2.81 in |
| Depth | 10.668 mm 0.42 in |

Material Specifications

| | |
|----------------------|-----------------------------------------------------------------|
| Material Type | High-impact, flame retardant, thermoplastic, UL listed material |
|----------------------|-----------------------------------------------------------------|

Environmental Specifications

| | |
|----------------------------|--------|
| Environmental Space | Indoor |
|----------------------------|--------|

760249172 | FP-NLBL-1P-246

| | |
|----------------------------|-------------|
| Flammability Rating | UL 94 V-0 |
| Safety Standard | cUL US 1863 |

Packaging and Weights

| | |
|---------------------------|--------------------|
| Included | Mounting screw (2) |
| Packaging quantity | 1 |
| Packaging Type | Bag |
| Weight, net | 0.036 kg 0.08 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--------------------------------------------------------------------------------------------------------------------------------|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |



* Footnotes

| | |
|-----------------|----------------------------------------------------------------------|
| Warranty | For more information, please consult our Product Warranty guidelines |
|-----------------|----------------------------------------------------------------------|