








Entry Boots and Wall/Roof Feed-through Plates
for Coaxial Cable

Bulletin 7545175 Revision D Page 1 of 2


Andrew Institute offers installation training.




Part Number	Description
SEC-614	Snap-in entry cushion 6 X 1/4"
SEC-638	Snap-in entry cushion 6 X 3/8"
SEC-412	Snap-in entry cushion 4 X 1/2"
SEC-358	Snap-in entry cushion 3 X 5/8"
SEC-378	Snap-in entry cushion 3 X 7/8"
SEC-1114	Snap-in entry cushion 1 X 1 1/4"
SEC-1158	Snap-in entry cushion 1 X 1 5/8"
SEC-1214	Snap-in entry cushion 1 X 2 1/4"



4" (102 mm) Ports					
Part #	Style	Wall Opening Size, in (mm)		Overall Size, in. (mm)	
		Width	Height	Width	Height
204673-1	1X1	4" (102 mm)	4" (102 mm)	7" (178 mm)	7" (178 mm)
204673-2	1X1	4" (102 mm)	4" (102 mm)	5.5" (140 mm)	5.5" (140 mm)
204673-2A	1X2	10" (254 mm)	4" (102 mm)	7" (178 mm)	7" (178 mm)
204673-3	1X3	15" (381 mm)	4" (102 mm)	20" (508 mm)	9.5" (241 mm)
204673-4	1X4	20.5" (521 mm)	4" (102 mm)	25.5" (648 mm)	9.5" (241 mm)
204673-6	2X3	15" (381 mm)	9.5" (241 mm)	23" (584 mm)	17.5" (445 mm)
204673-8	2X4	20.5" (521 mm)	9.5" (241 mm)	25.5" (648 mm)	17.5" (445 mm)
204673-9	3X3	15" (381 mm)	15" (381 mm)	23" (584 mm)	23" (584 mm)
204673-10	2X5	26" (660 mm)	9.5" (241 mm)	31" (787 mm)	17.5" (445 mm)
204673-12	3X4	20.5" (521 mm)	15" (381 mm)	25.5" (648 mm)	25.5" (648 mm)
204673-16	4X4	20.5" (521 mm)	20.5" (521 mm)	25.5" (648 mm)	25.5" (648 mm)
204673-18	3X6	31.5" (521 mm)	15" (381 mm)	39.5" (1003 mm)	25.5" (648 mm)
204673-20	4X5	26" (660 mm)	20.5" (521 mm)	31" (787 mm)	28.5" (724 mm)
204673-24	4X6	31.5" (521 mm)	20.5" (521 mm)	39.5" (1003 mm)	31" (787 mm)




Apply sealant to frame and plate
 Applique sellador al armazón y a la placa
 Appliquez le produit d'étanchéité sur la charpente et la plaque
 Dichtungsmittel auf Rahmen und Platte auftragen.
 applicare del sigillante sulla struttura e sulla piastra
 Aplicar vedante na moldura e na placa
 在框架與金屬板上塗上密封劑




Apply tar to roof and metal flashing
 Coloque breva asfáltica en el techo y tapajuntas metálicas
 Appliquez du goudron sur le toit et le solin métallique
 Bitumenanstrich auf Dach- und Metallanschlußflächen auftragen
 Applicare del catrame sul tetto o sulla conversa metallica
 Aplicar piche no teto e no metal polido
 在屋頂與金屬防水板上塗上焦油

Apply sealant to bottom and top of wood frame
 Aplique sellador a la parte superior e inferior del armazón de madera
 Appliquez le produit d'étanchéité au niveau des parties inférieure et supérieure de la charpente en bois
 Dichtungsmittel auf Unter- und Oberseite des Holzrahmens auftragen
 Applicare del sigillante sulla parte inferiore e superiore della struttura in legno
 Aplicar vedante na parte superior e inferior da moldura de madeira
 在木框的底部與頂部塗上密封劑

Roof
 Techo
 Toit
 Dach
 Tetto
 Teto
 屋頂



Apply sealant to screws and edges of plate
 Aplique sellador a los tornillos y a los bordes de la placa
 Appliquez le produit d'étanchéité sur les vis et les bords de la plaque
 Dichtungsmittel auf Schrauben und Plattenkanten auftragen
 Applicare del sigillante sulle viti e sui bordi della piastra
 Aplicar vedante nos parafusos e nas bordas da placa
 在螺絲與金屬板的邊緣上塗上密封劑



Flange cap
 Cubierta de brida
 Garniture à bride
 Verschlusskappe mit Bund
 Tappo per flangia
 Cobertura da flange
 法蘭蓋

ANDREW an Amphenol company
 2601 Telecom Parkway, Richardson, Texas, 75082, USA
 www.andrew.com

Technical Support
 +1 888 297 6433, Option 3 (Toll Free US and Canada)
 awpnarsupport@andrew.com

Notice: ANDREW disclaims any liability or responsibility for the results of improper or unsafe installation, inspection, maintenance, or removal practices.
 Aviso: ANDREW no acepta ninguna obligación ni responsabilidad como resultado de prácticas incorrectas o peligrosas de instalación, inspección, mantenimiento o retiro.
 Avis: ANDREW décline toute responsabilité pour les conséquences de procédures d'installation, d'inspection, d'entretien ou de retrait incorrectes ou dangereuses.
 Hinweis: ANDREW lehnt jede Haftung oder Verantwortung für Schäden ab, die aufgrund unsachgemäßer Installation, Überprüfung, Wartung oder Demontage auftreten.
 Atenção: A ANDREW abdica do direito de toda responsabilidade pelos resultados de práticas inadequadas e sem segurança de instalação, inspeção, manutenção ou remoção.
 Avvertenza: ANDREW declina eventuali responsabilità derivanti dall'esecuzione di procedure di installazione, ispezione, manutenzione e smontaggio improprie o poco sicure.
 注意: ANDREW 公司申明對於不恰當或不安全的安裝、檢驗、維修或拆卸操作所導致的後果不負責任。任何義務和責任。

©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners.