


UGBKIT-0412-T



Tinned Copper Ground Buss Bar, 1/4 in x 4 in x 12 in (6.4 mm x 101.6 mm x 304.8 mm)

Product Classification

| | |
|----------------------|--------------------------------------|
| Product Type | Grounding bar |
| Product Brand | HELIAX® |
| Ordering Note | CommScope® standard product (Global) |

Dimensions

| | |
|--|----------------------------|
| Height | 101.6 mm 4 in |
| Length | 304.8 mm 12 in |
| Material Thickness | 6.35 mm 0.25 in |
| Hole Size | 7/16 in 7/16 in x 5/8 in |
| Hole Distance, center to center | 19.05 mm 0.75 in |

Material Specifications

| | |
|----------------------|---------------|
| Material Type | Tinned copper |
|----------------------|---------------|

Packaging and Weights

| | |
|---------------------------|--|
| Height, packed | 454.66 mm 17.9 in |
| Width, packed | 248.92 mm 9.8 in |
| Length, packed | 50.8 mm 2 in |
| Included | Galvanized angle adapter Grounding bar Insulators Mounting brackets Universal hardware |
| Packaging quantity | 1 |
| Weight, gross | 3.36 kg 7.408 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

UGBKIT-0412-T

Included Products

- GB-HK-DPU – Universal Buss Bar Installation Hardware Kit, UL467 Compliant

GB-HK-DPU



Universal Buss Bar Installation Hardware Kit, UL467 Compliant

Product Classification

| | |
|----------------------|---|
| Product Type | Attachment kit |
| Product Brand | HELIAX® |
| Ordering Note | CommScope® standard product in the United States and Canada |

General Specifications

| | |
|--------------------|----------------|
| Accessories | Grounding Bars |
|--------------------|----------------|

Packaging and Weights

| | |
|---------------------------|--|
| Height, packed | 170.18 mm 6.7 in |
| Width, packed | 129.54 mm 5.1 in |
| Length, packed | 99.06 mm 3.9 in |
| Included | Angle adapters Drive pin anchor Insulators, Mounting brackets Universal hardware |
| Packaging quantity | 1 |
| Weight, gross | 2.6 kg 5.732 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|---|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

