



## SL-Series Modular Jack, RJ45, Cat6A Shielded, Blue (24 ea/pkg)

- Part of CommScope's initiative of removing single-use plastics which also includes copper panels, jacks, cords and faceplates

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America

### Portfolio

NETCONNECT®

### Product Type

Modular jack

### Product Series

SLX Series

## General Specifications

### ANSI/TIA Category

6A

### Cable Type

Shielded

### Color

Blue

### Conductor Type

Solid | Stranded

### Integrated Dust Cover Type

None

### Mounting

SL Series faceplates and panels

### Outlet Type

Standard

### Termination Punchdowns, minimum

5 times

### Termination Tool

SL Termination tool

### Termination Type

IDC

### Transmission Standards

ANSI/TIA-568-C.2 | ISO/IEC 11801 Class EA

### Wiring

T568A | T568B

## Dimensions

### Panel Cutout, recommended

14.78 x 20.07 mm (0.58 x 0.79 in)

### Panel Thickness, recommended

1.6 mm | 0.063 in

### Height

16.13 mm | 0.635 in

### Width

14.44 mm | 0.569 in

### Depth

36.8 mm | 1.449 in

### Compatible Cable Diameter, maximum

8.5 mm | 0.335 in

# 4-2153449-BL | ECO SLX-6AS-BL-24

<b>Compatible Insulated Conductor Diameter, maximum</b>	1.6 mm   0.063 in
<b>Contact Plating Thickness</b>	1.27 µm
<b>Compatible Conductor Gauge, solid</b>	26–22 AWG
<b>Compatible Conductor Gauge, stranded</b>	26–24 AWG

## Electrical Specifications

<b>Remote Powering</b>	Fully supports the safe delivery of power over LAN cabling described by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC 60512-99-002
<b>PoE Durability</b>	Supports IEEE 802.3bt Type 4 (90 W) applications greater than 3000 plug to jack mating cycles

## Material Specifications

<b>Contact Base Material</b>	Beryllium copper
<b>Contact Plating Material</b>	Gold
<b>Material Type</b>	PC+ABS   Zamak

## Mechanical Specifications

<b>Plug to Jack Mating Cycles</b>	Complies to IEC 60603-7 series
-----------------------------------	--------------------------------

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Flammability Rating</b>	UL 94 V-0

## Packaging and Weights

<b>Packaging Material</b>	Eco-friendly, single-use plastics-free
<b>Packaging quantity</b>	24
<b>Packaging Type</b>	Bag   Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

