

RR-APEX4-E



Apex RRU Mount for up to 4 Ericsson Radios - Mounts to Extended Spine on G2RHDX & RHDXL Series Mounts

Designed for G2 RHDX Series Mounts with Extended Spine

- Increased versatility and stability
- More RRU mounting available, reducing need for additional mounts
- Features integrated lifting points for safe and efficient hoisting of radios to the mounting location
- Supports all typical RRH units from Ericsson, ERS and RRUS
- Better load management and Less structure stress
- Angled RRU brackets for stronger, more versatile mounting
- Decreased PIM from radio relocation (pulls radio from near field)
- Decreased antenna pipe loading
- Compatible with towers and monopoles
- FITS 2-3/8" OD ~ 6" OD PIPES
- FOR 90 DEGREE ANGLES UP TO 4.5"
- FOR 60 DEGREE ANGLES UP TO 6.0"

Product Classification

Product Type	Remote radio head unit mount
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Mounting	Round and angle legs
-----------------	----------------------

Dimensions

Height	388.62 mm 15.3 in
Platform Width	441.96 mm 17.4 in
Length	1,031.24 mm 40.6 in
Mounting Diameter, maximum	152.4 mm 6 in
Mounting Diameter, minimum	60.325 mm 2.375 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

RR-APEX4-E

Wind Rating

For Specifications, please contact your local ANDREW representative

Packaging and Weights

Included

Clamps | Hardware

Packaging quantity

2

Weight, net

21.473 kg | 47.34 lb

* Footnotes

Warranty

For more information, please consult our Product Warranty guidelines

Wind Rating

BWS—Base Wind Speed; FBC—Florida Building Code