


SFG22HDX-13-4-H10



G22HDX Tower Sector Frame with extended face, 13 ft x 2.88 in OD face pipes. Base Kit Only. Includes four 2.88 OD x 120 in antenna pipes

Product Classification

Product Type	High capacity Tower sector frame
Product Brand	PIM-guard
Product Series	G2

General Specifications

Mounting	Angle 60°, 203.2 mm (8 in) Straight or tapered legs up to 203.2 mm (8 in) OD
Pipe, quantity	4
Sectors, quantity	1
Tower Taper	Non-tapered Tapered

Dimensions

Face Width	3,962 mm 13 ft
Width	3,962.4 mm 156 in
Face Support Pipe Diameter	73.025 mm 2.875 in
Mounting Diameter, maximum	218.44 mm 8.6 in
Mounting Diameter, minimum	38.1 mm 1.5 in
Pipe Outer Diameter	73.025 mm 2.875 in
Stand-off Distance	1,066.8 mm 42 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating	For Specifications, please contact steelproducts@commscope.com or call 800-255-1479
--------------------	--

Packaging and Weights

Included	Frame Plain end pipes (4) Stiff arms (2) Tower attachment
-----------------	---

SFG22HDX-13-4-H10

Packaging quantity 1
Weight, net 319.978 kg | 705.43 lb

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code