

760255888 | HCA-ACC-3mm SC/APC Test Lead 20FT, 2x Cvtr



HCA-ACC-3mm SC/APC Test Lead 20FT, Full size and DLX converter included

- Prodigy converters simplify installation and maintenance by reducing splicing requirements in the distribution portion of the network

Product Classification

Regional Availability	North America
Product Type	Fiber test patch cord
Product Brand	PRODIGY™
Product Series	HCA
Government Requirements	Build America Buy America (BABA) compliant*

General Specifications

Color, boot A	Black
Color, connector A	Black
Color, connector B	Green
Interface, Connector A	Prodigy
Interface, Connector B	SC/APC
Jacket Color	Yellow

Dimensions

Cable Assembly Length	6.096 m 20 ft
------------------------------	-----------------

Mechanical Specifications

Dust Cap Pulling Force, minimum	445 N 100.04 lbf
--	--------------------

Optical Specifications

Insertion Loss, maximum	0.3 dB
Insertion Loss, typical	0.15 dB
Return Loss, minimum	65 dB

Environmental Specifications

760255888 | HCA-ACC-3mm SC/APC Test Lead 20FT, 2x Cvtr

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Indoor/Outdoor
Qualification Standards	IEC 60793 IEC 60794