

SSH-158-3



SnapStak® Hanger for 1-5/8 in coaxial cable, triple stack capability, includes reinforcement bar

Product Classification

Product Type	Hanger kit
Product Brand	SnapStak®
Ordering Note	ANDREW® standard product (Global)

General Specifications

Cables per Hanger	1
Color	Silver
Hanger Type	Snap-in hanger
Mounting	3/4 in drilled cable ladder

Dimensions

Maximum Stack Height	3
Height	40.9 mm 1.61 in
Width	50.8 mm 2 in
Length	89.9 mm 3.539 in
Compatible Cable Diameter Range	49–51.1 mm
Compatible Diameter, maximum	51.1 mm 2.012 in
Compatible Diameter, minimum	49 mm 1.929 in
Nominal Size	1-5/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

SSH-158-3

Vibration Survival

≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation

≥500 hours in salt spray chamber

Environmental Strength Capability

Double cable weight

Packaging and Weights

Height, packed

22 cm | 8.661 in

Width, packed

15 cm | 5.906 in

Length, packed

14.4 cm | 5.669 in

Packaging quantity

10

Weight, gross

0.6 kg | 1.323 lb

Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

Included Products

SSHR-10

–

SnapStak Hanger Reinforcement Bar, PIM free bar provides the ability to add an additional cable run to the stack

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

SSHR-10



SnapStak Hanger Reinforcement Bar, PIM free bar provides the ability to add an additional cable run to the stack

Product Classification

Product Type	Adapter
Product Brand	SnapStak®
Ordering Note	ANDREW® standard product in the United States and Canada

General Specifications

Accessories	Adapters
Color	Black
Mounting	3/4 in through hole

Dimensions

Height	76.2 mm 3 in
Width	25.4 mm 1 in
Length	6.35 mm 0.25 in

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Mechanical Specifications

Maximum Loading	Quadruple stack for SSH-M Triple stack for hangers SSH-XL, SSH-L Triple stack, 1-5/8 in cable
Vibration Survival	≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
UV Resistance, minimum with no degradation	≥1000 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	17 cm 6.693 in
-----------------------	------------------

SSHR-10

Width, packed	13 cm 5.118 in
Length, packed	10 cm 3.937 in
Packaging quantity	10
Weight, gross	0.15 kg 0.331 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

