

# HR300B



Heat Regenerated Dehydrator, 19 in rack mountable, 3.0 kPa (0.44 psig), with low pressure, high pressure, high humidity, power and system failure alarms, 110-240 VAC: 48 Vdc

## Product Classification

<b>Product Type</b>	Dehydrator
<b>Warranty</b>	Three years from date of ship

## General Specifications

<b>Alarm Type</b>	High humidity   High pressure   Low pressure   Power failure   System failure
<b>Cut In/Out Pressure Type</b>	Continuous (default set to 3.0 kPa   0.4 psig)
<b>Dehydrator Type</b>	Automatically regenerating Desiccant
<b>Dew Point</b>	Better than -45 °C (-49 °F) at 80% RH at +20 °C (+68 °F)
<b>Flow Rate, nominal</b>	5 SLPM
<b>High-Humidity Alarm</b>	10% ±2% RH, threshold
<b>High-Pressure Alarm</b>	Factory set 8.5 psi
<b>Low-Pressure Alarm</b>	Factory set 1.5 psi
<b>Mounting</b>	Rack
<b>Port Count</b>	6
<b>Port Type</b>	3/8 in PE tube
<b>Power Cord</b>	USA power cord
<b>Power-Fail Alarm</b>	Loss of input power
<b>Rack Type</b>	EIA 19 in   ETSI N3
<b>Rack Units</b>	3
<b>Regulated Output Pressure Type</b>	Factory set, continuous

## Dimensions

<b>Product Height</b>	132 mm   5.197 in
<b>Product Width</b>	487 mm   19.173 in
<b>Product Depth</b>	360 mm   14.173 in

## Electrical Specifications

# HR300B

---

<b>Alarm Contact Rating</b>	Handles at least 0.5 A (ac or dc)
<b>Power Consumption, ac</b>	100 W
<b>Power Consumption, dc</b>	60 W
<b>Voltage</b>	110/240 Vac   48/60 Vdc

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +50 °C (+14 °F to +122 °F)
------------------------------	--------------------------------------

## \* Footnotes

<b>Warranty</b>	For more information, please consult our Product Warranty guidelines
-----------------	--