

XP-RM3U-12C



CommScope XPND™ 3Ru empty panel, accepts 12 XPND modular cassettes, providing up to 144 SC ports or 288 LC ports

- Components can be installed and removed from front or rear of panel
- Supports 12f and 24f applications while maintaining full panel density
- Cable mounting system allows for multiple trunk cables to be routed in the rear of panel

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber patch panel
Product Brand	CommScope XPND™

General Specifications

Color	White
Interface, front	Unloaded
Rack Type	EIA 19 in
Rack Units	3
Shelf Movement	Fixed
Total Ports, quantity	0

Dimensions

Height	44 mm 1.732 in
Width	431.8 mm 17 in
Depth	304.8 mm 12 in

Material Specifications

Material Type	Aluminum Steel
---------------	------------------

Packaging and Weights

Packaging quantity	1
Weight, net	5.375 kg 11.85 lb

Regulatory Compliance/Certifications

XP-RM3U-12C

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

