760179556 | 1291B GRN C6A 4/23 F/UTP R3000



GigaSPEED X10D® 1291B ETL Verified Category 6A F/UTP Cable, nonplenum, green jacket, 4 pair count, 3000 ft (914 m) length, reel

Product Classification

Regional Availability	Asia Australia/New Zealand Latin America North America		
Portfolio	SYSTIMAX®		
Product Type	Twisted pair cable		
Product Brand	GigaSPEED X10D®		
General Specifications			
Product Number	1291B		
ANSI/TIA Category	6A		
Cable Component Type	Horizontal		
Cable Type	F/UTP (shielded)		
Conductor Type, singles	Solid		
Conductors, quantity	8		
Drain Wire Type	Solid		
Jacket Color	Green		
Pairs, quantity	4		
Separator Type	Isolator		
Transmission Standards	ANSI/TIA-568.2-D		
Dimensions			
Cable Length	914.4 m 3000 ft		
Cable Length Tolerance	±5%		
Diameter Over Jacket, nominal	7.518 mm 0.296 in		
Jacket Thickness	0.508 mm 0.02 in		
Conductor Gauge, singles	23 AWG		
Drain Wire Gauge	26 AWG		

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 17, 2024



760179556 | 1291B GRN C6A 4/23 F/UTP R3000

Cross Section Drawing

Outer Jacket	
Insulation ———	
Separator	
Conductor	
Core Wrap	
Shield	
Drain Wire	

Electrical Specifications

dc Resistance Unbalance, maximum	4 %		
dc Resistance, maximum	8 ohms/100 m 2.438 ohms/100 ft		
Dielectric Strength, minimum	1500 Vac 2500 Vdc		
LP (Limited Power) Rating	0.5 A		
Mutual Capacitance at Frequency	5.6 nF/100 m @ 1 kHz		
Nominal Velocity of Propagation (NVP)	68 %		
Operating Frequency, maximum	500 MHz		
Operating Voltage, maximum	80 V		
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A		

Material Specifications

Conductor Material	Bare copper
Drain Wire Material	Tinned copper
Insulation Material	Polyolefin
Jacket Material	PVC
Separator Material	Polyolefin
Shield (Tape) Material	Polyester/Aluminum shield

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 17, 2024



760179556 | 1291B GRN C6A 4/23 F/UTP R3000

Mechanical Specifications

Pulling Tension, maximu	m	11.34 kg 25 lb
Environmental S	pecifications	
Installation temperature		0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature		-20 °C to +60 °C (-4 °F to +140 °F)
Environmental Space		Non-plenum
Flame Test Method		CMR
Packaging and V	Veights	
Cable weight		52.086 kg/km 35 lb/kft
Packaging Type		Reel
Regulatory Compliance/Certifications		
Agency	Classification	

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 17, 2024

